

1" x 1" (1000 lp/inch), Ronchi Ruling



Stock #56-600 CLEARANCE **20+ In Stock**

⊖ 1 ⊕ **A\$414⁴⁰**

ADD TO CART

Volume Pricing	
Qty 1+	A\$414.40 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Physical & Mechanical Properties

Dimensional Tolerance (inches):
±0.02

Dimensions (inches):
1 x 1

Thickness (mm):
1.50

Parallelism (arcmin):

±60

Dimensional Tolerance (mm):

± 0.02

Line to Line Parallelism (arcsec):

≤2

Parallelism of Pattern to Substrate (°):

±1

Optical Properties

Coating:

Vacuum Deposited Chrome, OD >3.0

Substrate:

Float Glass

Optical Density OD (Average):

3.00

Surface Quality:

20-10

Frequency (lp/inch):

1000.00

Surface Flatness (P-V):

1λ

Regulatory Compliance

RoHS 2015:

[Compliant](#)

Certificate of Conformance:

[View](#)

Reach 240:

[Compliant](#)

Product Details

- Chrome on Glass
- High Tolerance
- Superior to Etched and Filled Rulings
- Lines Parallel to Edge
- English and Metric Versions Available

High Precision Ronchi Rulings are excellent for evaluating resolution, field distortion, and parfocal stability. The glass targets are coated with vacuum-deposited chrome and have a float glass substrate. English and Metric version are available with various Linepairs Per Inch (LPI) and Linepairs Per Millimeter (lp/mm) measurements. High Precision Ronchi Rulings are offered in 0.5", 1", 2", and 4" squares.