

1" x 1" (50 lp/mm), Ronchi Ruling



Stock #58-779 3-5 DAYS

-

1

+

A\$441.60

ADD TO CART

Qty 1-4

A\$441.60

Qty 5+

A\$420.48

Volume Pricing

[Request Quote](#)

Get Product Downloads

Coating:
Vacuum Deposited Chrome, OD >3.0

Dimensional Tolerance (inches):
±0.02

Frequency (lp/mm):
50

Substrate:
Float Glass

Optical Density OD (Average): 3.00
Dimensions (inches): 1 x 1
Surface Quality: 60-40
Thickness (mm): 1.50
Type: Metric
Dimensional Tolerance (mm): ± 0.02
Line to Line Parallelism (arcsec): ≤2
Parallelism of Pattern to Substrate (°): ±1
Surface Flatness (P-V): 1λ

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View