

1X 120mm WD, In-Line Illumination Telecentric Lens



Stock #59-741 3-5 DAYS

- 1 + **A\$2,472.00**

ADD TO CART

Qty 1+
A\$2,472.00

Volume Pricing
Request Quote

Get Product Downloads

Length (mm): 137.00
Ferrule Diameter (inches): 0.312
Horizontal Field of View, 1/2" Sensor: 6.4mm
Horizontal Field of View, 2/3" Sensor: 8.8mm
Maximum Diameter (mm): 29.5

Horizontal Field of View @ Max Sensor Format: 8.8mm
Type: Telecentric Lens
Primary Magnification PMAG: 1X
Maximum Sensor Format: 2/3"
Working Distance (mm): 120.00
Mount: C-Mount
Style: In-Line Illumination
Aperture (f/#): f/16.6
Distortion (%): ≤0.1
Compatible Light Guide/Source: 1/4" (0.312")
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View