

1X Mitutoyo Plan Apo Infinity Corrected Long WD Objective

See More by [Mitutoyo](#)



1X Mitutoyo Plan Apo Infinity Corrected Long WD Objective, #58-235

Stock **#58-235** 3-5 DAYS

⊖ 1 ⊕

A\$4,104.00

ADD TO CART

Qty 1+

A\$4,104.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Horizontal Field of View, 1/2" Sensor:
6.40mm

Horizontal Field of View, 2/3" Sensor:
8.80mm

Focal Length FL (mm):
200.00

Model Number:

378-800-12
Length excluding Threads (mm): 84.00
Magnification: 1X
Maximum Diameter (mm): 31.5
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.025
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 11.0
Depth of Field (µm): 440.00
Field of View, 24 Diameter Field Eyepiece (mm): 24.00
Field of View, 18 Diameter Field Eyepiece (mm): 18.00
Operating Temperature (°C): +5 to +40
Operating Humidity: 20 - 80%
Working Distance (mm): 11.0
Weight (g): 300.00
Wavelength Range (nm): 435 - 655
Style: Infinity Corrected
Manufacturer: Mtutoyo
Parfocal Length (mm): 95
Immersion Liquid: N/A
Exit Pupil Diameter (mm): 10.00

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)