

2" Fiber Optic Diffuse Axial Illuminators



2" Fiber Optic Diffuse Axial Illuminators (#53-380)

Stock **#53-380** 3-5 DAYS

- 1 + **A\$1,408.00**

ADD TO CART

Qty 1+
A\$1,408.00
Volume Pricing
Request Quote

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Numerical Aperture NA:
0.55 nominal

Fiber Diameter (µm):
50 (0.002" nominal)

Construction:
Black Anodized Aluminum

Packing Fraction (%):
83% nominal

Transmission Loss: 10% per ft. at 660nm
Type of Illumination: Fiber Optic Light Guide
Geometry: Diffuse Axial

Regulatory Compliance

Reach 174: Compliant
RoHS: Not Compliant
Certificate of Conformance: View
