

2.00", English Rotary Stage



Stock #33-465 **1 In Stock**

A\$1,816⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$1,816.00 each
Need More?	Request Quote

Product Downloads

General

English **Type:**

Physical & Mechanical Properties

1 **Weight (lbs):**

44.4 x 44.4 **Stage Size (mm):**

1.75 x 1.75 **Stage Size (inches):**

Construction:

Aluminum top and base; steel tangent arm drive

Center Hole:
0.25" Dia. Thru

Travel (°):
±5 (Fine), 360 (Coarse)

Increments (arcmin):
12

Load Capacity, Normal (lbs):
10

Load Capacity, Vertical (lbs):
4

Type of Movement:
Rotary

Guide System:
Ball Bearing

Table Diameter (inches):
2

Hardware & Interface Connectivity

Type of Drive:
Tangent Arm

Threading & Mounting

Mounting Threads:
(12) 6-32 on 0.625", 1.125" & 1.50" dia. B.C.

Regulatory Compliance

RoHS 2015:
Compliant

Certificate of Conformance:
[View](#)

Product Details

- Low Wear, Low Friction Movement with Coarse or Fine Adjustment
- 2 or 2.62" Diameter Stages with Tapped Mounting Holes
- Calibrated Dial with 12 Minute Vernier for Accurate Read-Out

Compact miniature stages provide low-friction rotary movement with both coarse and fine adjustment. This allows for quick rotation over a continuous 360° travel, plus precise angular adjustment at any selected position. Features include preloaded angular contact ball bearing system, a positive position lock, a 2.00" or 2.62" diameter stage with tapped mounting holes and a calibrated dial with six minute vernier for accurate positional read-out. It can be combined with our compatible linear translation stages for multi-axis linear-rotary applications.

Technical Information

