

20 lp/mm, 1" x 3", Float Glass, Ronchi Ruling



Stock **#38-259** CLEARANCE **5 In Stock**

-

1

+

A\$145^{.85}

A\$291.70

ADD TO CART

Volume Pricing	
Qty 1-4	A\$291.70 A\$145.85 each
Qty 5+	A\$279.35 A\$139.18 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

Physical & Mechanical Properties	
3.00	Length (inches):
12.7 x25.4	Pattern Size (mm):
	Thickness (mm):

1.10	
	Width (inches):
1.00	
Optical Properties	
	Coating:
Vacuum Deposited Chrome	
	Frequency (lp/mm):
20.00	
	Substrate:
Float Glass	
	Optical Density OD (Average):
3.00	
Regulatory Compliance	
	RoHS 2015:
Compliant	
	Certificate of Conformance:
View	
	Reach 240:
Compliant	

PRODUCT DETAILS

- Used for Evaluation of Resolution, Field Distortion, and Parfocal Stability
 - Ideal for Reticle and Field Calibration Requirements
 - Available on Float Glass, Fused Silica, Fused Silica with Fluorescent Backing, and [Opal](#).
- Precision Ronchi Ruling Glass slides are excellent for evaluating resolution, field distortion, and parfocal stability, especially of microscopes. Many different Linepairs Per Millimeter (lp/mm) versions available.