

20 lp/mm 1" x 3", Opal Glass Ronchi Ruling Slide



Stock **#59-546** 3 In Stock

-

1

+

A\$505^{.60}

ADD TO CART

Volume Pricing	
Qty 1-4	A\$505.60 each
Qty 5+	A\$482.40 each
Need More?	Request Quote

Product Downloads

General

Note:

Pattern Location is Centered

NIST Certification:

No

Physical & Mechanical Properties

Dimensional Tolerance (inches):

±0.100

Length (mm):

25.40

12.7 x25.4	Pattern Size (mm):
1.52 ±0.100	Thickness (mm):
76.20	Width (mm):
±0.001	Line Width Tolerance (µm):

Optical Properties

Vacuum Deposited Chrome	Coating:
20.00	Frequency (lp/mm):
Opal Glass	Substrate:
>3.0	Optical Density OD (Average):
40-20	Surface Quality:

Regulatory Compliance

Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 235:

Product Details

Opal Glass material has been discontinued by the manufacturer and may be available in limited quantities. [Contact us](#) for more information.

- Chrome on Opal
- Test Resolution of Reflective Systems
- High Tolerance