

20° Travel, 60 x 60mm Stage Size Metric Goniometer, R130.4



Stock #13-630 3-5 DAYS

- 1 +

A\$1,251.20

ADD TO CART

Qty 1-4
A\$1,251.20
Qty 5+
A\$1,126.08
Volume Pricing
Request Quote

Get Product Downloads

Type of Movement:
Goniometer

Guide System:
Dovetail

Type of Drive:
Lead Screw

Type:
Metric

Stage Size (mm): 60 x 60
Travel (°): ±10
Construction: Brass Stage
Load Capacity (kg): 5
Mounting Threads: (1) M6 x 1.0, (8) M4 x 0.7
Radius R (mm): 130.4
Resolution (°): 0.1
Weight (kg): 0.70

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
