

20 x 28.28 x 2.5mm Elliptical Beamsplitter 50R/50T



Stock #27-609 CLEARANCE 3-5 DAYS

-

1

+

A\$39.92

ADD TO CART

Qty 1+

A\$39.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Clear Aperture (%):
80.00

Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR ¼λ MgF₂ @ 550nm

Dimensional Tolerance (mm):
±0.25

Dimensions (mm):
20.0 x 28.28

Major Axis (mm):
28.28

Minor Axis (mm): 20.00
Reflection (%): 50.00
Substrate: ☐ N-BK7
Thickness (mm): 2.50
Thickness Tolerance (mm): ±0.25
Transmission (%): 50.00

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View
