

## 200mm Dia x 600mm Focal Length, MgF<sub>2</sub> Coated, PCX Condenser Lens



Stock #19-916 3-5 DAYS

-

1

+

A\$832.00

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| A\$832.00                     |
| Qty 11+                       |
| A\$752.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

Diameter (mm):  
200.00 +0.0/-0.5

Effective Focal Length EFL (mm):  
600.00 @ 587.6nm

Back Focal Length BFL (mm):  
586.00

Coating:  
MgF<sub>2</sub> (400-700nm)

|                                                                           |
|---------------------------------------------------------------------------|
| <div>Coating Specification:<br/>R<sub>avg</sub> ≤1.75% @400 - 700nm</div> |
| <div>Substrate: <div><div></div><div>N-BK7</div></div></div>              |
| <div>Surface Quality:<br/>120-80</div>                                    |
| <div>Center Thickness CT (mm):<br/>21.60</div>                            |
| <div>Edge Thickness ET (mm):<br/>5.03</div>                               |
| <div>Radius R<sub>1</sub> (mm):<br/>310.00</div>                          |
| <div>Clear Aperture CA (mm):<br/>195</div>                                |
| <div>f#:<br/>3.00</div>                                                   |
| <div>Numerical Aperture NA:<br/>0.17</div>                                |
| <div>Type:<br/>Condenser Lens</div>                                       |
| <div>Bevel:<br/>Protective bevel as needed</div>                          |
| <div>Wavelength Range (nm):<br/>400 - 700</div>                           |

## Regulatory Compliance

|                                                 |
|-------------------------------------------------|
| <div>RoHS 2015:<br/>Compliant</div>             |
| <div>Certificate of Conformance:<br/>View</div> |
| <div>Reach 235:<br/>Compliant</div>             |