

TECHSPEC[®] 20.0mm Dia. x 70.0mm FL, Uncoated, Plano-Convex Lens



Stock #32-936 3-5 DAYS
[Other Coating Options](#)

-

1

+

A\$46.40

ADD TO CART

Qty 1-9
A\$46.40
Qty 10+
A\$41.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
20.00 +0.0/-0.025

Effective Focal Length EFL (mm):
70.00 @ 587.6nm

Back Focal Length BFL (mm): 68.03
Coating: Uncoated
Substrate:  N-BK7
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): <1
Center Thickness CT (mm): 3.00 ±0.10
Edge Thickness ET (mm): 1.59
Radius R₁ (mm): 36.18
Clear Aperture CA (mm): 19
f#: 3.5
Numerical Aperture NA: 0.14
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 350 - 2200

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View