

2.00", English Rotary Stage



Stock #33-465 3-5 DAYS



1



A\$1,385.60

ADD TO CART

Qty 1+
A\$1,385.60

Volume Pricing
Request Quote

Get Product Downloads

Mounting Threads:
(12) 6-32 on 0.625", 1.125" & 1.50" dia. B.C.

Type:
English

Weight (lbs):
1

Stage Size (mm):
44.4 x 44.4

Stage Size (inches):
1.75 x 1.75

Construction: Aluminum top and base; steel tangent arm drive
Center Hole: 0.25" Dia. Thru
Travel (°): ±5 (Fine), 360 (Coarse)
Type of Drive: Tangent Arm
Increments (arcmin): 12
Load Capacity, Normal (lbs): 10
Load Capacity, Vertical (lbs): 4
Type of Movement: Rotary
Guide System: Ball Bearing
Table Diameter (inches): 2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View