

20mm Dia. Left-Handed Plastic Circular Polarizer (CP42HE)



Stock **#88-096** 3-5 DAYS

- 1 +

A\$46.40

ADD TO CART

Qty 1-5
A\$46.40
Qty 6+
A\$38.40
Volume Pricing
Request Quote

Get Product Downloads

Diameter (mm): 20.00
Substrate: CP42HE on PMMA
Operating Temperature (°C): -40 to +80
Thickness (mm): 2.29 ±0.24

Transmission (%) : 42.00
Type : Left-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film on PMMA
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
#Sorting : 2.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Compliant