

TECHSPEC[®] 2.0mm Dia. x 1.5mm FL, Uncoated, Plano-Convex Lens



Stock **#43-396** 3-5 DAYS
[Other Coating Options](#)

-

1

+

A\$102.40

ADD TO CART

Qty 1-9
A\$102.40
Qty 10+
A\$92.00
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
2.00 +0.0/-0.025

Effective Focal Length EFL (mm):
1.50 @ 587.6nm

Back Focal Length BFL (mm): 1.07
Coating: Uncoated
Substrate: 
Surface Quality: 20-10
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Focal Length Tolerance (%): ±1
Centering (arcmin): 30-45, typical
Center Thickness CT (mm): 0.80 ±0.05
Edge Thickness ET (mm): 0.32
Radius R₁ (mm): 1.28
Clear Aperture CA (mm): 1.5
f#: 0.75
Numerical Aperture NA: 0.67
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 400 - 2500

Regulatory Compliance

RoHS 2015: Compliant
Reach 219: Compliant
Certificate of Conformance: View