

20" x 24" UV Filter Sheet



Stock **#39-426** **5 In Stock**

-

1

+

A\$47^{.20}

ADD TO CART

Volume Pricing	
Qty 1+	A\$47.20 each
Need More?	Request Quote

Product Downloads

General

Type:

Longpass Filter

Physical & Mechanical Properties

Dimensions (mm):

508.0 x609.6

Length (mm):

609.60

Dimensions (inches):

20 x24

Width (mm):

508.00	
Optical Properties	
400.00	Cut-On Wavelength (nm):
Polyester Film	Substrate: ☐
Clear	Color:
200 - 750	Wavelength Range (nm):
Regulatory Compliance	
Compliant	Reach 191:
Compliant	RoHS 2015:
View	Certificate of Conformance:

Product Details

- Virtually Transparent, Flexible Polyester Filter
- Deep-Dyed PET Substrate to Absorb UVA, UVB, and UVC Rays
- <10% Transmission Below 390nm

Flexible Thin Film UV Filters block UVA, UVB, and UVC wavelengths while transmitting visible illumination. These filters are ideal for applications where ultraviolet rays have harmful effects.

Technical Information

