

TECHSPEC® 20X Arcturus® HeNe Beam Expander



20XHeNe Fixed Beam Expander, #55-579

Stock #55-579 3-5 DAYS

1 A\$1,152.00

ADD TO CART

Qty 1-4
A\$1,152.00
Qty 5+
A\$1,014.40
Volume Pricing
Request Quote

Get Product Downloads

Angle of Incidence (°):
0

Coating:
BBAR (450-750nm)

Design Wavelength DWL (nm):
633

Entrance Aperture (mm):

Exit Aperture (mm):
27

Expansion Power:
20X

Focus Range:
1.2m - ∞

Substrate: ☐
Optical Glass

Length (mm):
122.50

Mounting Threads:
C-Mount

Type:
Beam Expander

Weight (g):
474

Housing Diameter (mm):
50

Transmitted Wavefront, P-V:
<λ/4 @ 633nm for Input Beam ≤1mm

Coating Specification:
R_{abs} <0.4% @ 630 - 670nm
R_{avg} <0.6% @ 450 - 750nm

Wavelength Range (nm):
450 - 750

Style:
Fixed Magnification

Divergence Adjustment:
Non-Rotating Optics

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)
