


20X Mitutoyo Telecentric Objective

See More by [Mitutoyo](#)



3X (#56-985) & 5X (#56-986)



Stock **#87-228** 3-5 DAYS



1



A\$4,211.20

ADD TO CART

Qty 1+

A\$4,211.20

Volume Pricing

[Request Quote](#)

Get Product Downloads

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Focal Length FL (mm):
9.21

Model Number:

375-051
Length (mm): 90.00
Length excluding Threads (mm): 90.00
Magnification: 20X
Maximum Diameter (mm): 39
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.42
Mounting Threads: M26 x 36 TPI
Type: Microscope Objective
Resolving Power (µm): 0.7
Depth of Field (µm): 1.60
Field of View, 24 Diameter Field Eyepiece (mm): 1.2
Field of View, 18 Diameter Field Eyepiece (mm): 0.9
Operating Temperature (°C): +5 to +40
Operating Humidity: 20 - 80%
Working Distance (mm): 20
Weight (g): 310
Note: Image is formed 280mm from specimen (170mm from the mounting flange)
Wavelength Range (nm): 435 - 655
Style: Finite Conjugate
Manufacturer: Mitutoyo
Parfocal Length (mm): 110
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View