

## 22.2mm Aperture UV/VIS Fiber Optic Collimator, SMA



Fiber Optic Collimator, SMA (SMA adapter inserted)



Stock **#17-567** 3-5 DAYS

- 1 +

**A\$816.00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| A\$816.00                     |
| Qty 11+                       |
| A\$720.00                     |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

### Get Product Downloads

Diameter (mm):

28.58

Substrate: ☐

[Fused Silica](#) (Corning 7980)

Type:

|                                                                                                                                        |
|----------------------------------------------------------------------------------------------------------------------------------------|
| Fiber Collimator                                                                                                                       |
| <b>Wavelength Range (nm):</b><br>190 - 1250                                                                                            |
| <b>Aperture Size:</b><br>22.2                                                                                                          |
| <b>Compatible Fiber NA:</b><br>0.22                                                                                                    |
| <b>Connector:</b><br>SMA                                                                                                               |
| <b>Fiber Diameter (µm):</b><br>800 - 1000                                                                                              |
| <b>Focal Length FL (mm):</b><br>38.00                                                                                                  |
| <b>Housing Material:</b><br>Stainless Steel                                                                                            |
| <b>Length (mm):</b><br>52.83                                                                                                           |
| <b>Note:</b><br>Compatible with <a href="#">#17-573</a> , <a href="#">#17-574</a> , & <a href="#">#17-575</a><br>Refocusing Assemblies |
| <b>Operating Temperature (°C):</b><br>-40 to 100                                                                                       |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |