

## 2.25" x 2.70", 2.0" FL, Cylinder Fresnel Lens



Cylinder Fresnel Lenses

Stock **#46-112** **4 In Stock**

⊖ 1 ⊕ A\$112<sup>00</sup>

**ADD TO CART**

### Volume Pricing

Qty 1-10	A\$112.80 each
Qty 11-49	A\$100.80 each
Need More?	<a href="#">Request Quote</a>

### Product Downloads

### General

Fresnel Lens **Type:**

### Physical & Mechanical Properties

0.06 **Center Thickness CT (inches):**

±0.05 **Dimensional Tolerance (inches):**

**Dimensions (inches):**

2.25 x 2.7

**Dimensions (mm):**

57.15 x 68.58

**Effective Size (inches):**

2.0 x 2.7

**Thickness Tolerance (inches):**

±0.020

**Optical Properties**

**Effective Focal Length EFL (mm):**

50.80

**Substrate:**

Acrylic

**Coating:**

Uncoated

**Wavelength Range (nm):**

400 - 1100

**Effective Focal Length EFL (inches):**

2.00

**Groove Density (grooves/inch):**

200.00

**Index of Refraction (n<sub>d</sub>):**

1.49

**Transmission (%):**

85 (Typical)

**Environmental & Durability Factors**

**Operating Temperature (°C):**

80 (Maximum)

**Regulatory Compliance**

**RoHS 2015:**

[Compliant](#)

**Certificate of Conformance:**

[View](#)

**Reach 242:**

[Compliant](#)

**Product Details**

- Collapsed Version of a Standard Cylinder Lens
- Ideal for Focusing One Dimension
- Various Sizes Available

**Technical Information**

