

Richardson Gratings™ 2400 Grooves, 30 x 30mm, 200-800nm, Plane Holographic
Reflection Grating

See More by [Richardson Gratings™](#)



Richardson Gratings™ High Precision Reflective Holographic Diffraction Gratings



Stock **#15-756** 3-5 DAYS

-

1

+

A\$280.00

ADD TO CART

Qty 1+

A\$280.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Groove Density (grooves/mm):
2400

Wavelength Range (nm):
200 - 800

Blaze Wavelength (nm): 270
Dimensions (mm): 30.0 x 30.0 ±0.1
Clear Aperture (%): >90
Coating: Aluminium
Construction: Holographic Grating
Length (mm): 30.00
Substrate: Float Glass
Thickness (mm): 6.00 ±0.5
Type: Reflective Diffraction Grating
Width (mm): 30.00
Reflected Wavefront, RMS: λ/4
Centering of Ruled Area on Substrate (mm): ±1
Alignment of Grooves to Edge (°): ±0.15
Groove Spacing Tolerance (%): <0.05
Polarization: S, P and Average
Master Reference: 420H
Spectral Order (m): 1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View