

24V CCS Digital Power Supply, 28 Watt

See More by [CCS](#)



Digital Version

Stock **#35-334** **1 In Stock**

-

1

+

A\$784^{.00}

ADD TO CART

Volume Pricing	
Qty 1+	A\$784.00 each
Need More?	Request Quote

Product Downloads

General	
256 steps	Intensity Control Option:
3	Number of Channels:
Power Supply	Type of Illumination:
Note: Compatible to all High Angle, Low Angle and Diffuse Ring Lights, as well as up to 100 x 100mm Backlights and R75 Dome Lights.	

Strobe Lighting Time Range:	
40μs - 40ms (10 steps)	
Physical & Mechanical Properties	
84 W x 120 H x 83 D	Dimensions (mm):
	Weight (kg):
0.6	
Electrical	
Power Consumption (W):	
78	
Regulatory Compliance	
Certificate of Conformance:	
View	

Product Details