

2.5 OD, 25.4mm Dia., Reflective Neutral Density Filter



Stock #27-932

CLEARANCE

3-5 DAYS

-

1

+

A\$23.92

ADD TO CART

Qty 1+

A\$23.92

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):

25.40 ±0.3

Optical Density OD (Average):

2.5

Substrate:

Borosilicate

Coating:

Metallic Based ND

Thickness (mm):

1.00

Thickness Tolerance (mm):	±0.25
Transmission (%):	0.3
Type:	Neutral Density Filter
Parallelism (arcmin):	±3
Dimensional Tolerance (mm):	±0.3
Clear Aperture (%):	>90
Optical Density Tolerance (%):	±10

Regulatory Compliance

RoHS:	Compliant
Certificate of Conformance:	View