

TECHSPEC® 2.5 OD 25mm Diameter, Reflective ND Filter



Stock #43-811

CLEARANCE

3-5 DAYS

-

1

+

A\$80.00

ADD TO CART

Qty 1-5

A\$80.00

Qty 6+

A\$64.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):

25.00

Angle of Incidence (°):

0

Optical Density OD (Average):

2.5

Substrate: Float Glass
Coating: Surface 1: Inconel
Reflection (%) 55.00
Surface Quality: 80-50
Thickness (mm): 1.60 Nominal
Transmission (%) 0.3
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Dimensional Tolerance (mm): ±0.5
Clear Aperture (%) 80
Neutrality: ±5% of Optical Density
Note: Optical density values are average over specified blocking wavelength range.
Surface Flatness (P-V): 4 - 6λ

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant