

25 x 38mm, 30R/70T, Plate Beamsplitter



Stock **#46-667** 3-5 DAYS

-

1

+

A\$88.00

ADD TO CART

Qty 1-9

A\$88.00

Qty 10+

A\$67.20

Volume Pricing

[Request Quote](#)

Get Product Downloads



Coating Specification:

Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: $\lambda/4$ MgF₂ @ 550nm

Construction:

Plate

Dimensional Tolerance (mm):

±0.38

Dimensions (mm): 25.0 x 38.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 30/70
Substrate: ☐ Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant