

TECHSPEC[®] 25/25.4mm Diameter, C-Mount Thick Optic Mount



Stock #56-354

CONTACT US

-

1

+

A\$158⁴⁰

ADD TO CART

Volume Pricing	
Qty 1-4	A\$158.40 each
Qty 5-9	A\$140.64 each
Qty 10-25	A\$129.92 each
Need More?	Request Quote

Product Downloads

SPECIFICATIONS

General

Type:

Fixed

Type of Optics:

Circular	
Optic Mount (Fixed)	Function:
Physical & Mechanical Properties	
24.2	Extension Length (mm):
Black Anodized Aluminum (6061 T6)	Construction:
28.2	Total Length (mm):
30.0	Outer Diameter (mm):
22.00	Clear Aperture CA (mm):
11.5	Max. Thickness of Compatible Optics (mm):
3.3	Min. Thickness of Compatible Optics (mm):
Threading & Mounting	
25.0 - 25.4	Diameter of Compatible Optics (mm):
C-Mount	Thread Type:
Regulatory Compliance	
Compliant	RoHS 2015:
View	Certificate of Conformance:
Compliant	Reach 250:

PRODUCT DETAILS

25/25.4mm holder is a 3 part assembly and adds 24.2mm to the system length.

- Mounts for Simple Lenses, Achromats, Filters, or Reticles
- Designed to Integrate with Any C, S, or T-Mount Components
- Optic is Held in Place with Included Retaining Ring

TECHSPEC® C, S, and T-Mount Circular Optic Mounts are designed to mount a variety of circular optical components into C, S, or T-Mount compatible systems. An included threaded retainer ring, designed to accept a standard spanner wrench, securely holds the optical component. These circular optic mounts are compatible with a wide variety of Edmund Optics optomechanical components utilizing C, S, or T-Mount threads, such as [extension tubes](#) and [kinematic mounts](#). TECHSPEC® C, S, and T-Mount Circular Optic Mounts are threaded for 1" x 32TPI, M12 x 0.5, or M42 x 0.75 mounting, with 30mm, 16mm, and 48mm outer diameters, respectively. These mounts are ideal for creating and personalization of a diverse range of optical systems.

Note: [#56-353](#), [#56-354](#), [#52-933](#), and [#52-292](#) are all 3-part assemblies

TECHNICAL INFORMATION

