

25/25.4mm Diameter, E-Series Kinematic Mount, Quick Start Optical Mounts



#17-521: 25/25.4mm Diameter, E-Series Kinematic Mount



Stock **#17-521** [CONTACT US](#)

- 1 +

A\$124.80

ADD TO CART

Qty 1+
A\$124.80
Volume Pricing
Request Quote

Get Product Downloads

Type:
Adjustable - Tip-Tilt

Type of Optics:
Circular

Size of Compatible Optics (mm):
25.0 - 25.4

Number of Adjustment Screws:
2

Clear Aperture CA (mm): 23
Construction: Aluminum Plates, Stainless Steel Screws, and Brass Thread Bushings
Fine Tilt Angle (°): ±3.5
Fine Tip Angle (°): ±3.5
Adjustment Screw Pitch (mm): 0.25
Contents of Kit: #15-866 , #15-850
Compatible Post: M6 x 1.0, M4 x 0.7, 8-32
Min. Thickness of Compatible Optics (mm): 2
Optical Axis Height (mm): 127.00
Post Diameter (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant
