

25.4 x 25.4 x 3mm High Efficiency Window



Stock **#46-097** 3-5 DAYS

- 1 +

A\$34.40

ADD TO CART

Qty 1-5
A\$34.40
Qty 6+
A\$27.60
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0

Bevel:
Protective as needed

Clear Aperture (%):
≥90

Clear Aperture CA (mm):

22.86 x 22.86
Dimensions (mm): 25.40 x 25.40
Thickness (mm): 3.00 ±0.25
Coating: BBAR (425-700nm)
Coating Specification: R _{avg} ≤0.5% @ 425 - 700nm
Edges: Seamed
Substrate: Float Glass
Surface Quality: 80-50
Transmission (%): 95.6 Average (typical)
Type: Protective Window
Wavelength Range (nm): 425 - 700
Length (mm): 25.40
Width (mm): 25.40

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 2011: Compliant