

25.4 x 25.4mm Right-Handed Circular Polarizing Film (CP42HER)



Stock #11-047 CLEARANCE 3-5 DAYS

-

1

+

A\$17.52

ADD TO CART

Qty 1+

A\$17.52

Volume Pricing

[Request Quote](#)

Get Product Downloads

Substrate:

[Polymer Film CP42HER](#)

Length (mm):
25.40

Operating Temperature (°C):
-40 to +80

Dimensions (mm):
25.4 x 25.4

Thickness (mm):
0.27 ±0.04

Transmission (%) : 42.00
Type : Right-Handed Circular Polarizer
Dimensional Tolerance (mm) : +0.0/-0.3
Construction : Polarizing Film
Wavelength Range (nm) : 400 - 700
Polarization Efficiency (%) : >99.90
Heat Resistance (°C x Hours) : 80 x 500
Width (mm) : 25.40
#Sorting : 14.00

Regulatory Compliance

RoHS 2015 : Compliant
Certificate of Conformance : View
Reach 235 : Contains SVHC(s)