

[All Products](#) / [Optics](#) / [Optical Mirrors](#) / [Flat Mirrors](#) / [Float Glass](#) / [4-6λ First Surface Mirrors](#)

[See all 61 Products in Family](#)

254 x 356mm, 4-6λ Mirror



4-6λ First Surface Mirrors

Stock **#85-036** 3-5 DAYS



1



A\$364.80

ADD TO CART

Qty 1-5

A\$364.80

Qty 6+

A\$292.00

Volume Pricing

[Request Quote](#)

Get Product Downloads

Surface Flatness (P-V):

4 - 6λ

Substrate: ☐

Float Glass

Surface Quality:

80-50

Dimensions (mm):

254.0 x 356.0 ±0.76
Coating Specification: R _{avg} >85% @400 - 700nm
Coating: Protected Aluminum (400-700nm)
Coating Type: Metal
Angle of Incidence (°): 45.00
Bevel: Protective as needed
Clear Aperture (%): >90
Thickness (mm): 6.00
Type: Flat Mirror
Wavelength Range (nm): 400 - 700
Length (mm): 356.00
Width (mm): 254.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant