

254 x 356mm, 50R/50T, Plate Beamsplitter



Stock **#46-584** 3-5 DAYS

- 1 +

A\$964.80

ADD TO CART

Qty 1-9
A\$964.80
Qty 10+
A\$721.60
Volume Pricing
Request Quote

Get Product Downloads



Coating Specification:
Surface 1: Dielectric, ±5% R/T @ 550nm
Surface 2: AR 1/λ MgF₂ @ 550nm

Construction:
Plate

Dimensional Tolerance (mm):
±0.38

Dimensions (mm): 254.0 x356.0
Edges: Cut
Reflection/Transmission Ratio (R/T): 50/50
Substrate: Float Glass
Surface Flatness (P-V): 4 - 6λ
Surface Quality: 80-50
Thickness (mm): 3.00
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant