

TECHSPEC[®] 25.4mm Dia., 6.35mm Thick, 1064nm, λ/10 N-BK7 Window



TECHSPEC λ/10 Laser Line Coated Windows

Stock #38-979 CLEARANCE 3-5 DAYS

-

1

+

A\$175.92

ADD TO CART

Qty 1+

A\$175.92

Volume Pricing

[Request Quote](#)

Get Product Downloads



Angle of Incidence (°):

0

Clear Aperture CA (mm):

22.86

Coating:

Laser V-Coat (1064nm)

Design Wavelength DWL (nm):

1064

Diameter (mm):

25.40 +0.00/-0.10
Substrate: N-BK7
Index of Refraction n_d: 1.516
Surface Quality: 10-5
Thickness (mm): 6.35 ±0.20
Type: Laser Line Window
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%) : 90
Abbe Number (v_d): 64.17
Coating Specification: R _{abs} <0.25% @ 1064nm
Surface Flatness (P-V): λ/10
Damage Threshold, By Design: 15 J/cm² @ 1064nm, 20ns, 20Hz
Edges: Fine Ground

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View