

TECHSPEC[®] 25.4mm Dia., 3.18mm Thick, Fused Silica Uncoated Laser Window Substrate



TECHSPEC[®] Uncoated Laser Window Substrates

Stock #37-694 3-5 DAYS

- 1 +

A\$232.00

ADD TO CART

Qty 1-5

A\$232.00

Qty 6+

A\$208.80

Volume Pricing

[Request Quote](#)

Get Product Downloads



Clear Aperture CA (mm):
22.86

Coating:
Uncoated

Diameter (mm):
25.40 +0.00/-0.10

Substrate: Fused Silica (Coming 7980)
Index of Refraction n_d: 1.458
Surface Quality: 10-5
Thickness (mm): 3.18 ±0.20
Type: Laser Window Substrate
Parallelism (arcmin): <3
Bevel: Protective as needed
Clear Aperture (%): 90
Abbe Number (v_d): 67.8
Wavelength Range (nm): 200 - 2200
Surface Flatness (P-V): $\lambda/10$
Fused Silica Grade: 7980 0F
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View