


25.4mm Dia 50R/50T, VIS-NIR Polka-Dot Beamsplitters



VIS-NIR Polka-Dot Beamsplitters

Stock #15-981 3-5 DAYS

- 1 + **A\$217.60**

ADD TO CART

Qty 1-10
A\$217.60
Qty 11+
A\$184.96
Volume Pricing
Request Quote

Get Product Downloads



Angle of Incidence (°):
0 - 45

Center to Center Spacing (mm):
0.15

Clear Aperture (%):
90

Coating: Square Aluminum (AlMgF ₂) Apertures
Construction: Polka-Dot
Diameter (mm): 25.40 +0.0/-0.5
Minimum Aperture (mm): 2.00
Operating Temperature (°C): 150 Maximum
Parallelism (arcmin): <3
Reflection/Transmission Ratio (R/T): 50/50
Reflection/Transmission Tolerance (%): ±5 @ 45°
Substrate: ☐ B270
Surface Quality: 80-50
Thickness (mm): 1.65 ±0.1
Type: Standard Beamsplitter
Wavelength Range (nm): 400 - 2000

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View