

25.4mm Dia., 600 - 950nm, Complementary Chirped Mirror Pair

See More by [UltraFast Innovations \(UFI\)](#)



UltraFast Innovations (UFI) Ultra-Broadband Complementary Chirped Mirror Pairs

Stock #17-064 3-5 DAYS

1

A\$2,414.40

ADD TO CART

Qty 1-9
A\$2,414.40
Qty 10+
A\$2,176.00
Volume Pricing
Request Quote

Get Product Downloads



Wedge (arcmin):
10 ±5

Clear Aperture (%):
80

Back Surface:
Commercial Polish

Coating Specification: R _{avg} >99% @ 600 - 950nm (5° AOI, p-polarization)
GDD Specification: -50fs ² @ 600 - 950nm (5° AOI, p-polarization)
Wavelength Range (nm): 600 - 950
Irregularity (P-V) @ 632.8nm: λ/10
Coating Type: Dielectric
Coating: Complementary Chirped Pair (600 - 950nm)
Diameter (mm): 25.40 +0.00/-0.05
Thickness (mm): 6.35 ±0.20
Angle of Incidence (°): 5
Substrate: ☐ Fused Silica (Corning 7980)
Note: Sold as a Set of 2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant