



25.4mm Dia. Protected Aluminum Coated, Mounted Fused Silica Corner Cube Retroreflector



Mounted Fused Silica Corner Cube Retroreflectors

Stock **#15-820** [CONTACT US](#)

− 1 +

A\$720.00

ADD TO CART

Qty 1-5
A\$720.00
Qty 6+
A\$576.00
Volume Pricing
Request Quote

Get Product Downloads

Beam Deviation (arcsec):
±3

Coating:
Aluminum with protective overcoat

Diameter Tolerance (mm):

+0.0/-0.1
Substrate: Fused Silica (Coming 7980)
Inner Diameter (mm): 25.4
Outer Diameter (mm): 38.1
Surface Quality: 20-10
Mounting Threads: (2) 1/4-20 Tapped Holes
Type: Retroreflector
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height: ±0.25
Image Orientation: Left-Handed
Coating Specification: Reflective Surfaces: R _{avg} >85% FROM400-700nm, @ 45° AOI
Ray Deviation (°): 180
Wavelength Range (nm): 400 - 700
Power (fringes) @ 632.8nm: 0.20
Irregularity (fringes) @ 632.8nm: 0.20

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View