

TECHSPEC®

25.4mm Dia., Uncoated, IR Ultrafast Thin Window



Stock #11-753

3-5 DAYS

-

1

+

A\$192.00

ADD TO CART

Qty 1-5

A\$192.00

Qty 6+

A\$172.80

Volume Pricing

Request Quote

Get Product Downloads



Coating:

Uncoated

Diameter (mm):

25.40 +0.00/-0.10

Substrate:

Fused Silica IR Grade

Index of Refraction n_d :

1.458
Surface Quality: 20-10
Thickness (mm): 1.00 ±0.10
Type: Ultrafast Window
Bevel: Protective as needed
Clear Aperture (%): 90
Transmitted Wavefront, P-V: λ/6
Abbe Number (v_d): 67.8
Parallelism (arcsec): ≤30
Wavelength Range (nm): 200 - 3500
Fused Silica Grade: 7979 0G
Edges: Fine Ground
Type of Window: Glass

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View