

TECHSPEC®

25.4mm Dia., Uncoated, Linear Glass Polarizer (XP42)



Stock #19-645 3-5 DAYS

-

1

+

A\$216.00

ADD TO CART

Qty 1-9
A\$216.00
Qty 10+
A\$190.40
Volume Pricing
Request Quote

Get Product Downloads



Coating:
Uncoated

Diameter (mm):
25.40

Extinction Ratio:
9000:1 @ 546nm

Substrate:

[XP42](#) Laminated Between Glass

Operating Temperature (°C):
-10 to +55

Thickness (mm):
2.00 ±0.10

Transmission (%):
42 @ 546nm

Type:
Linear Polarizer

Dimensional Tolerance (mm):
+0.00/-0.20

Construction:
Laminated Glass Polarizing Film

Wavelength Range (nm):
400 - 700

Polarization Efficiency (%):
>99.98 @ 546nm

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 235:
[Compliant](#)