

TECHSPEC®

25.4mm Dia. x 35mm FL, Uncoated, ZnSe Plano-Convex Lens

See More by [Coherent®](#)



TECHSPEC Zinc Selenide (ZnSe) Plano-Convex (PCX) Lenses

Stock **#39-531** 3-5 DAYS

[Other Coating Options](#)

- 1 +

A\$504.00

ADD TO CART

Qty 1-10

A\$504.00

Qty 11+

A\$453.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40 +0.00/-0.10

Effective Focal Length EFL (mm):
35.00 @ 10.6µm

Back Focal Length BFL (mm): 33.46
Coating: Uncoated
Substrate:  Coherent® Infrared ZnSe
Surface Quality: 40-20
Power (P-V) @ 632.8nm: λ
Power (P-V) @ 10.6μm: λ 10
Irregularity (P-V) @ 10.6μm: λ 20
Centering, ETD (μm): ≤12.7
Center Thickness CT (mm): 3.70 ±0.10
Edge Thickness ET (mm): 2.03
Radius R₁ (mm): 49.10
Clear Aperture CA (mm): 22.86
f/#: 1.38
Numerical Aperture NA: 0.36
Type: Plano-Convex Lens
Bevel: Protective bevel as needed
Wavelength Range (nm): 600 - 18000
Bulk Absorption Coefficient (cm⁻¹): <0.0005 @ 10.6μm
Surface Roughness (Angstroms): <50 RMS

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View