

TECHSPEC®

25.4mm Dia x 75mm FL, Uncoated Imaging Grade PCX Cylinder Lens



Stock #34-612 3-5 DAYS

-

1

+

A\$142.40

ADD TO CART

Qty 1-5
A\$142.40
Qty 6+
A\$113.60
Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
25.40 +0.0/-0.025

Effective Focal Length EFL (mm):
75.00

Substrate: N-BK7

f/#:

3.00
Numerical Aperture NA: 0.17
Coating: Uncoated
Type: Cylinder Lens, Plano-Convex
Wavelength Range (nm): 350 - 2200
Back Focal Length BFL (mm): 72.93
Bevel: Protective bevel as needed
Center Thickness CT (mm): 3.14
Center Thickness Tolerance (mm): ±0.1
Clear Aperture CA (mm): 22.86
Edge Thickness ET (mm): 1.00
Focal Length Tolerance (%): ±1
Radius R₁ (mm): 38.76
Surface Quality: 40-20
Power (P-V) @ 632.8nm: 1.5λ
Irregularity (P-V) @ 632.8nm: λ/4
Plano Axis Wedge (arcmin): <5
Power Axis Wedge (arcmin): <5

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View