

25.4mm Diameter Unmounted 0.04-3.0 OD, Circular Variable Neutral Density (ND) Filter



Unmounted Circular Variable Neutral Density (ND) Filters

Stock #43-761

3-5 DAYS



1



A\$444.80

ADD TO CART

Qty 1-10

A\$444.80

Qty 11+

A\$400.32

Volume Pricing

[Request Quote](#)

Get Product Downloads

Angle of Incidence (°):

0.00

Optical Density OD (Average):

0.04 - 3.0

Substrate: ☐

[B270](#)

Inner Diameter (mm):

7.5
Coating: Variable
Outer Diameter (mm): 25.4
Surface Quality: 60-40
Thickness (mm): 1.52
Thickness Tolerance (mm): ±0.25
Type: Neutral Density Filter
Blocking Wavelength Range (nm): 400 - 700
Parallelism (arcmin): ±3
Dimensional Tolerance (mm): ±0.10 ID, ±0.20 OD
Optical Density Tolerance (%): ±5
Linearity (%): ±5
Coating Specification: Continuously Variable Inconel from 0 - 270°
Mount: Unmounted

Regulatory Compliance

Reach 181: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View