

TECHSPEC®

25.4mm Protected Gold λ /10 Knife-Edge Pickoff Mirror



25.4mm Enhanced Protected Gold λ /10 D-Shaped Pickoff Mirror, #36-136

Stock **#36-136** 3-5 DAYS



1



A\$160.00

ADD TO CART

Qty 1-5

A\$160.00

Qty 6+

A\$144.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.40

Surface Flatness (P-V):
 λ /10

Substrate: ☐
[Fused Silica](#) (Coming 7980)

Back Surface: Fine Grind
Surface Quality: 20-10
Dimensional Tolerance (mm): +0.0/-0.20
Coating Specification: R _{avg} >96% @ 700 - 2000nm R _{avg} >96% @ 2000 - 10,000nm
Coating: Protected Gold (700-10000nm)
Coating Type: Metal
Bevel: Protective bevel as needed
Edges: Ground
Parallelism (arcmin): 2
Thickness (mm): 6.35
Thickness Tolerance (mm): ±0.20
Type: Flat Mirror
Wavelength Range (nm): 700 - 10000
Damage Threshold, Reference:  0.8 J/cm ² @ 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant