

25/25.4mm ID, Precision Gimbal Mount, Quick Start Optical Mounts



#17-534 and #17-513



Stock **#17-517** [CONTACT US](#)

- 1 +

A\$756.96

ADD TO CART

Qty 1+
A\$756.96

Volume Pricing
Request Quote

Get Product Downloads

Type:
Adjustable - Gimbal

Type of Optics:
Circular

Size of Compatible Optics (mm):
25.0 - 25.4

Clear Aperture CA (mm):
22.0

Coarse Rotation (°): 360
Fine Tilt Angle (°): ±6
Fine Tip Angle (°): ±6
Contents of Kit: #54-999 , #16-308 , #16-329 , #15-849
Compatible Post: M6 x 1.0
Max. Thickness of Compatible Optics (mm): 6.0
Optical Axis Height (mm): 127.00
Type of Adjustment Screws: Micrometer
Post Diameter (mm): 25.4

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant