

TECHSPEC[®] 25.4mm Silver and NIR II Coated, Mounted Corner Cube Retroreflector



Mounted N-BK7 Corner Cube Retroreflectors



Stock #12-672 3-5 DAYS

-

1

+

A\$632.00

ADD TO CART

Qty 1-5

A\$632.00

Qty 6+

A\$505.60

Volume Pricing

[Request Quote](#)

Get Product Downloads



Beam Deviation (arcsec):
±3

Coating:
NIR II & Silver with protective overcoat

Diameter Tolerance (mm): +0.0/-0.1
Substrate: N-BK7
Inner Diameter (mm): 25.40
Outer Diameter (mm): 38.10
Surface Quality: 60-40
Mounting Threads: (2) 1/4-20 Tapped Holes
Type: Retroreflector
Housing Tolerance (mm): Outer Diameter: +0/-0.5, Height: ±0.25
Image Orientation: Left-Handed
Coating Specification: Reflective Surfaces: $R_{abs} > 97\%$ FROM400 - 2500nm @ 0° AOI $R_{avg} > 98\%$ FROM400 - 2500nm @ 0° AOI Entrance: $R_{abs} \leq 1.5\%$ @ 750 - 800nm, $R_{abs} \leq 1.0\%$ @ 800 - 1550nm, $R_{avg} \leq 0.7\%$ @ 750 - 1550nm
Ray Deviation (°): 180
Wavelength Range (nm): 750 - 1550
Surface Flatness (P-V): $\lambda/8$

Regulatory Compliance

RoHS 2015: Not Compliant
Certificate of Conformance: View