

254nm CWL, 40nm FWHM, 12.5mm Mounted Diameter



Stock #67-742 3-5 DAYS

[Additional Bandwidths](#)

-

1

+

A\$248.00

ADD TO CART

Qty 1-9

A\$248.00

Qty 10+

A\$222.40

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
12.50 +0.00/-0.25

Angle of Incidence (°):
0

Optical Density OD (Average):
≥4.0

Clear Aperture CA (mm): 9.0
Center Wavelength CWL (nm): 254.00 +10.0/-0.0
Center Wavelength CWL Tolerance (nm): +10.0/-0.0
Full Width-Half Max FWHM (nm): 40.00 ±8
Full Width-Half Max FWHM Tolerance (nm): ±8
Minimum Transmission (%): >20
Operating Temperature (°C): -50 to +50
Coating: Traditional Coated
Surface Quality: 80-50
Type: Bandpass Filter
Typical Applications: Mercury Emission
Blocking Wavelength Range (nm): 200 - 10000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 3.5

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant
