

2.5mm CA, A-25H0-P10 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series, 6 pins FPC with Thermistor



2.5mm CA, A-25H0-P10 Corning® Varioptic® Variable Focus Liquid Lens, Packaged A-Series, 6 pins FPC with Thermistor



Stock **#15-739** CLEARANCE 3-5 DAYS

- 1 + **A\$131.12**

ADD TO CART

Qty 1+
A\$131.12

Volume Pricing
Request Quote

Get Product Downloads



Diameter (mm):
9.40

Coating:
VS

Type: Packaged Lens w/ Thermistor
Clear Aperture CA (mm): 2.5
Contents of Kit: Packaged A-25H0 with a straight flex cable with thermistor FPC-A-10 (6 pins)
Focus Range: -5 to +13 diopter
Model Number: A-25H0-P10
Operating Temperature (°C): -30 to +85
Storage Temperature (°C): -40 to +85
Thickness (mm): 3.50
Transmission (%): 97 @ 587nm
Transmitted Wavefront Error, RMS: 30nm
Typical Applications: Compact optical systems such as barcode readers, industrial cameras, & medical imaging and biometrics systems

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View