

TECHSPEC® 25mm Cage System Iris, 0.8 - 12mm Aperture



Stock #88-199 **6 In Stock**

⊖ 1 ⊕ A\$248⁰⁰

ADD TO CART

Volume Pricing

Qty 1+	A\$248.00 each
Need More?	Request Quote

Product Downloads

General

Iris **Function:**

Number of Leaves: 10 **Note:**

Physical & Mechanical Properties

25.0 **Compatible Plate Inner Diameter (mm):**

17.20 **Length (mm):**

Inner Diameter (mm):

0.8 - 12

Black Anodized Aluminum

Construction:

31.5 Dia. **Dimensions (mm):**

12 **Maximum Aperture (mm):**

10 **Number of Leaves:**

Optical Properties

0.8 **Minimum Aperture (mm):**

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Reach 224:
[Compliant](#)

Certificate of Conformance:
[View](#)

Product Details

- 0.8 – 12mm Adjustable Aperture
- Smooth Operation from Maximum to Minimum Aperture
- Fits in Any 25mm Cage System Plate

The TECHSPEC® Cage System Iris is a 10-leaf, blued spring steel iris in an anodized aluminum housing that can be easily integrated into any 25mm TECHSPEC Cage System plate. The TECHSPEC Cage System Iris provides smooth transition from the maximum aperture of 12mm to the minimum aperture of 0.8mm. The iris can be used to adjust system performance by controlling system f#, field stop diameter, and overall energy throughput.

Technical Information

