

TECHSPEC® 25mm Cx Series Fixed Focal Length Lens



25mm Cx Series Fixed Focal Length Lens, #33-564

Stock **#33-564** 3-5 DAYS

1

A\$265.00

ADD TO CART

Qty 1+

A\$265.00

Volume Pricing

[Request Quote](#)

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Iris Option:
Fixed

Length (mm):
26.40

Horizontal Field of View, 1/2" Sensor:
36.7mm - 14.4°

Horizontal Field of View, 2/3" Sensor:
50.6mm - 19.7°

Filter Thread: M25.5 x0.50 with adapter #89-941
Maximum Diameter (mm): 30
Outer Diameter (mm): 30.0
Weight (g): 30
Horizontal Field of View, 1/3" Sensor: 27.5mm - 10.8°
Maximum Rear Protrusion (mm): 0
Maximum Image Circle (mm): 11.00
Numerical Aperture NA, Object Side: 0.042
Number of Elements (Groups): 7 (6)
Note: Cx Lens Accessory required for use. All field of view and working distance values listed assume a Cx Lens Accessory has been integrated. Cx Lens Accessory is not included and must be purchased separately.
Horizontal Field of View, 1/1.8" Sensor: 40.8mm - 15.5°
Horizontal Field of View, 1/2.5" Sensor: 32.6mm - 12.4°
Type: Fixed Focal Length Lens
Focal Length FL (mm): 25.00
Primary Magnification PMAG: 0.175
Maximum Sensor Format: 2/3"
Working Distance (mm): 150 - ∞
Mount: C-Mount
Aperture (f/#): Accessory Dependent
Coating: 425 - 675nm BBAR
Coating Specification: 425 - 675nm BBAR
Entrance Pupil Position (mm): 15.89
Object Space Principal Plane (mm): 18.77
Image Space Principal Plane (mm): -12.44
Field of View at Max Sensor Format: Horizontal: 50.7mm - 19.8° Vertical: 38mm - 14.9° Diagonal: 63.6mm - 24.6°
Maximum Distortion (%): 0.22
Exit Pupil Position (mm): -15.68
Lens Wavelength Range: VIS
Storage Temperature (°C): -20 to +60 For questions regarding operating temperature please contact our support team

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View