

TECHSPEC[®] 25mm Dia 0.15 NA, λ /40 Uncoated, UV Fused Silica Aspheric Lens



TECHSPEC UV Fused Silica Aspheric Lenses



Stock #17-331 3-5 DAYS

1

A\$1,160.00

ADD TO CART

Qty 1-5

A\$1,160.00

Qty 6+

A\$928.00

Volume Pricing

[Request Quote](#)

Get Product Downloads



Diameter (mm):
25.00 +0/-0.025

Effective Focal Length EFL (mm):
75.00 @ 355nm

Numerical Aperture NA: 0.15
Back Focal Length BFL (mm): 70.90
Substrate: ☐ Fused Silica (Corning 7980)
Aspheric Design Wavelength (nm): 355
Asphere Figure Error, RMS @ 632.8nm: λ/40
Coating: Uncoated
Centering (arcmin): <1
Surface Quality: 40-20
Clear Aperture CA (mm): 22.5
Edge Thickness ET (mm): 3.78
Center Thickness CT (mm): 6.00 ±0.1
f/#: 3
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Conjugate Distance: Infinite
Power (diopters): 13.33

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View