

TECHSPEC®

25mm Dia., 0.83 Numerical Aperture, Uncoated, Inked, High Precision Aspheric Lens



TECHSPEC® Precision Aspheric Lenses

Stock **#37-426-INK** 10-15 DAYS

[Other Coating Options](#)

- 1 + **A\$648.00**

ADD TO CART

Qty 1-5

A\$648.00

Qty 6+

A\$518.40

Volume Pricing

[Request Quote](#)

Get Product Downloads

Diameter (mm):
25.00 ±0.025

Effective Focal Length EFL (mm):
15.00 @ 587.6nm

Numerical Aperture NA:
0.83

Back Focal Length BFL (mm): 9.24
Substrate: N-SF6
Asphere Figure Error, RMS @ 632.8nm: 0.4λ
Coating: Uncoated
Centering (arcmin): <3
Surface Quality: 40-20
Clear Aperture CA (mm): 22.50
Edge Thickness ET (mm): 3.31
Center Thickness CT (mm): 10.40 ±0.10
f/#: 0.60
Bevel: Protective bevel as needed
Shape of Back Surface: Plano
Type: Aspheric Lens
Wavelength Range (nm): 390 - 2500
Conjugate Distance: Infinite

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View